NORO



LAKE SHOWER CABIN 90R

Item number: 66024

Practical and highly affordable shower cubicle of high quality. Easy to assemble and clean. Fully silicone-free. NORO Lake shower cubicle has a transparent glass front and back walls in glass with a discreet structure that conceals the underlying pipe. Supplied with 3-function shower set. Magnet function when closing. Spring loaded wheels with ball bearing. Suitable for mixers cc 150 and 160 mm for cubicle leadthrough ½. 5 mm safety glass. Aluminium profile. Tray in glass fibre reinforced acrylic. Rear walls in glass with a discrete structure, conceals underlying pipe.

Included articles

2438 1 x lake back walls 90x90r/c

2440 1 x lake tray 90x90r 2441 1 x lake door 90x90r

Detailed information

Item number		Material and surface treatment	
NOBB	53441038	Main material	PU reinforced acrylic, Safety
RSK	7365750	Surface treatment	glass, Aluminum Anodized
EAN	7340032403183	Glass	Clear glass
Standards and classifications		Color	Aluminum
EN standard	EN14428, EN14527	De deserte e discourate e and cost	La
CE marked	Yes	Packaging dimensions and weig	gnt 1,970
ETIM	EC010491	Package width (m)	
Burgland discounting and soutule		Package height(m)	0,900
Product dimensions and weight		Package depth(m)	0,970
Height (mm)	2040	Package weight(kg)	102,400
Height min. (mm)	2025	3 3 3	·
Height max. (mm)	2045		
Width	900		
Depth (mm)	900		
Glass thickness (mm)	5		
Net weight (kg)	96		

Care instructions

To facilitate the cleaning of shower doors and shower walls, the showers have large smooth surfaces and profiles without deep grooves. Discolouration is removed using citric or tartaric acid, rinse thoroughly afterwards. Limescale stains are removed using household vinegar warmed to 50 degrees: Rub it in, let it act, rinse away. Repeat for tough stains. Use rubbing alcohol to remove grease stains.